


EBC011



Splitter box

ZDO8H050MSS0000-00STAK190MSS



Application

Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes

Electrical data

Operating voltage	[V]	< 30 AC/DC; ("supply class 2" to cULus)
Max. current load per module/slot	[A]	4
Max. current load total	[A]	10

EBC011



Splitter box

ZDO8H050MSS0000-00STAK190MSS

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 67; ("enclosure type 1" according to cULus)
Mechanical data	
Weight [g]	303.5
Dimensions [mm]	33 x 60 x 152
Materials	PA
Number of ports splitter box	8
Connector type	M12
Accessories	
Accessories (supplied)	Protective caps: 2 labels: 8
Remarks	
Pack quantity	1 pcs.
Electrical connection - Connection	
Connector: 1 x M23; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm	



Splitter box

ZDO8H050MSS0000-00STAK190MSS

Connection

+ 19	1 (1...8) _C
- 6	3 (1...8) _C
⏚ 12	5 (1...8) _C
15	4 (1) _C
7	2 (1) _C
5	4 (2) _C
4	2 (2) _C
16	4 (3) _C
8	2 (3) _C
3	4 (4) _C
14	2 (4) _C
17	4 (5) _C
9	2 (5) _C
2	4 (6) _C
13	2 (6) _C
11	4 (7) _C
10	2 (7) _C
1	4 (8) _C
18	2 (8) _C

Electrical connection - slot

Connector: 8 x M12; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm

