

POTENTIAL TERMINAL BLOCK YE BLUE YE BLUE

Potential terminal block
yellow/blue/yellow/blue

[Link to Product](#)


Illustration



	00	01	02	03	04	05	06	07	08	09
X0	—————									
X1	—————									
X2	—————									
X3	—————									

Product may differ from Image

Approvals



Technical Data

Operating voltage	max. 30 V AC/DC
Total current	max. 10 A

General data

Protection	IP20
Connection	Spring clamp terminals: 0.08...2.5 mm ² (AWG 28...12)
Dimensions H × W × D	70×56×32.5 mm

Temperature range 0...+55 °C (storage temperature -40...+85 °C)

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1