



Datenblatt - Fiche technique - Data sheet

21.15.8708



ROLINE LWL-Kabel 50/125 μ m OM3, LC/LC, türkis, 10m

ROLINE Câble FO 50/125 μ m, LC/LC, OM3, turquoise, 10m

ROLINE Fibre Optic Jumper Cable, 50/125 μ m, LC/LC, OM3, turquoise, 10m

1 2 3 4 5 6

A

A


B

B

C

C

D



Specification:

- 1. Connector Type : LC Multimode
- 2. Cable Type :
 2-1 Zipcord Cable, $\phi 2.0\text{mm}$, 50/125um Multimode.(OM3 Corning Fiber)
 2-2 Calbe Jacket : Aqua Color, PVC Material.
- 3. Cable Marker
- 4. Shrink Tube
- 5. Length : xM(FT)

Performance:

- a. Insertion Loss : $< 0.5 \text{ dB}$
- b. Fiber Extention : $-0.05\text{um} < H < +0.05\text{um}$
- c. $\phi 1.25\text{mm}$ Ferrule End-face Radius : $7 < R < 25\text{mm}$
- d. Apex Offset : $< 50\text{um}$
- e. Increase in insertion loss after 500 mating : 0.2 dB Max
- f. Operating Temperature : $-20^\circ \text{ to } +70^\circ$
- g. Storage Temperature : $-40^\circ \text{ to } +80^\circ$

Remack#

21.15.8700	MultiMode, LC-LC,50/125 um	0.5M
21.15.8701	MultiMode, LC-LC,50/125 um	1M
21.15.8702	MultiMode, LC-LC,50/125 um	2M
21.15.8703	MultiMode, LC-LC,50/125 um	3M
21.15.8705	MultiMode, LC-LC,50/125 um	5M
21.15.8708	MultiMode, LC-LC,50/125 um	10M

GENERAL TOLERANCE OF DIMENSIONS X.XXX ±0.005 X.XX ±0.05 X.X ±0.1	DRAWING	07.JAN.2011	Abby	Rotronic Co.,Ltd.
	CHECK	07.JAN.2011	MAER	
	APPROVAL	07.JAN.2011	YTY	
	DATE		NAME	ITEM NO.: 21.15.XXXX 有吊卡
SCALE	1/1 (A4)	UNIT	mm	DES.: LC to LC Duplex patch cord
DRAWING NO.		SFNIE503131xxxx03001(SA1)		
DRAWING CLASSIFICATION		S	SHEET 1 OF 1	

1 2 0 3 4 10cm 5 6