



RE1080

- Epoxy fibre-glass FR4 0.80 mm
- Single-sided 35 µm Cu
- Without holes
- Surface chem. Ni/Au
- 12 self-adhesive strips in pitch 0.40 mm
- Pre-scratched rated break point for the separation of individual modules from the board
- Size 90 x 100 mm




RE1080

- Epoxydglashartgewebe FR4 0,80 mm
- Einseitig 35 µm Cu
- Keine Bohrungen
- Oberfläche aus chem. Ni/Au
- 12 selbstklebende Kontakteleisten im Pitch 0,40 mm
- Vorgeritzte Sollbruchstellen
- Größe 90 x 100 mm



RE1080

- Fibre de verre époxyde FR4 0,80 mm
- Simple face 35 µm Cu
- Sans trous
- Surface avec Ni/Au chimique
- 12 listeaux de contact autoadhésifs en pitch 0,40 mm
- Points destinés à la rupture
- Dimensions 90 x 100 mm



RE1080

- Fibra de vidrio epoxídica FR4 0,80 mm
 - Por dos lados 35 µm de Cu
 - Sin agujeros
 - Superficie terminal química de Ni/Au
 - 12 adaptadores autoadhesivos de pitch 0,40 mm
 - Punto de rotura controlada tallado
- Tamaño 90 x 100 mm