




**SPECIFICATION
CONTROL DRAWING
Crystal Resonator**

FREQUENCY
54.000000MHz



Holder Style	3X25X06 4-Pad
Mode	Fundamental
Adjustment Tolerance	± 15 PPM at 25°C
Temperature Stability	± 25 PPM
Operating Temp. Range	-10°C to +60°C
Load Capacitance	19 pF
ESR	15 Max Ohm
Drive Level	0.35 Max mW
Static Capacitance (C0)	3.0pF Max pF
Ageing	+/-3ppm 1st year max
Marking	AEL54.000 WWYY

Amdt Date	Change Note	AEL Code
		X54M000000S303
		Issue Ref A