

## Myriad Adjustable Round - White with Silver bezel

MYRIAD ADJ ROUND WHITE 4000K DALI SILVER BEZ  
2056215



### Product features

- The Myriad Adjustable Round recessed spotlight is a high efficient accent downlight, fixture color RAL 9016 - Traffic white / Bezel, correlated colour temperature of 4000K, color rendering index Ra92, fixture lumen 702lm, total power consumption 10W, luminaire efficacy 70 lm/W, nominal light beam angle 24°, mains voltage 230-240V~ AC, control technology type: DALI, product length 76mm, width 76mm, height 115mm, cut-out dimension 76mm, IP rating IP20, 5 years warranty.



### PRODUCT OVERVIEW

Product name	MYRIAD ADJ ROUND WHITE 4000K DALI SILVER BEZ
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Office, Residential & Consumer, Retail
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	702
Luminaire efficacy (lm/W)	70
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	24
Photobiological Risk Group	RG1
Total power consumption (W)	10
Electrical protection	Class II
Control gear type	Electronic ballast
Control gear mounting	Integral
Dimming method	DALI
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5025768562152

### DATA TABLE

#### General data

Product name	MYRIAD ADJ ROUND WHITE 4000K DALI SILVER BEZ
Technology	LED

## Myriad Adjustable Round - White with Silver bezel

*MYRIAD ADJ ROUND WHITE 4000K DALI SILVER BEZ*

### 2056215

<b>Housing</b>	PC Polycarbonate
<b>Mount</b>	Ceiling recessed mounting
<b>Environment</b>	Indoor
<b>General application</b>	Hospitality, Office, Residential & Consumer, Retail
<b>Performance ambient temperature Tq (°C)</b>	25
<b>ETIM Class</b>	EC001744
<b>Warranty</b>	5 years

#### Optical data

<b>Fixture luminous flux (lm)</b>	702
<b>Luminaire efficacy (lm/W)</b>	70
<b>LOR (%)</b>	100
<b>Colour temperature (K)</b>	4000
<b>Light colour</b>	Neutral White
<b>CRI (Ra)</b>	90
<b>Colour Variation Initial (SDCM)</b>	SDCM3
<b>Adjustable chromaticity</b>	N
<b>Beam Angle (°)</b>	24
<b>Distribution type</b>	Symmetric
<b>Photobiological Risk Group</b>	RG1

#### Electrical data

<b>Total power consumption (W)</b>	10
<b>Mains voltage (V)</b>	230-240V
<b>Electrical protection</b>	Class II
<b>Control gear type</b>	Electronic ballast
<b>Control gear mounting</b>	Integral
<b>Transformer required</b>	Yes
<b>Dimming method</b>	DALI
<b>Drive current (mA)</b>	250
<b>Energy Efficiency Class (A-&gt;G) of contained light source</b>	E
<b>Nominal Frequency (Hz)</b>	50/60Hz

#### Lifetime data

<b>Lifespan L70 B50</b>	100000
<b>Lifespan L80 B20</b>	100000
<b>Lifespan L90 B10</b>	68500

#### Physical data

<b>Housing colour</b>	White
<b>IP rating</b>	IP20
<b>IK rating</b>	IK02
<b>Diffuser material</b>	Glass
<b>Nominal Product Width (mm)</b>	76
<b>Nominal Product Height (mm)</b>	115
<b>Cutout Dimensions (W x L in mm or Diameter in mm)</b>	76
<b>Max. Lamp Diameter (mm) - D</b>	90


## Myriad Adjustable Round - White with Silver bezel MYRIAD ADJ ROUND WHITE 4000K DALI SILVER BEZ 2056215

Weight (kg)	0.38
Recessed Depth (mm)	115

### Packaging

Single packaging type	Carton
Product EAN number	5025768562152
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768562152
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

### PHOTOMETRY



Distance [m]	Cone diameter [m]	E(0°) E(C0)	12.9°	Illuminance [lx]
0.5	0.23	12208 5701		
1.0	0.46	3052 1425		
1.5	0.69	1366 633		
2.0	0.92	783 358		
2.5	1.15	498 231		
3.0	1.37	339 155		

Distance [m] Cone diameter [m] Illuminance [lx]  
C0 - C180 (Half beam angle: 25.8°)

### TECHNICAL DRAWINGS

