

## collet chuck DIN 6343 185 E, round

**ORION**<sup>®</sup>

### Execution:

- hardened and ground
- clamping bridge max. 0.1 mm of the nominal diameter
- concentricity
- $\varnothing$  1-10 mm  $\leq$  20  $\mu$ m
- $\varnothing$  11-30 mm  $\leq$  30  $\mu$ m
- $\varnothing$  31-60 mm  $\leq$  40  $\mu$ m
- up to  $\varnothing$  8 mm smooth bore, from  $\varnothing$  9 mm with crosswise grooves



<b>Art. no.</b>	<b>23354 680</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	23354680
<b>Outer diameter</b>	84 mm
<b>Diameter</b>	66 mm
<b>Length</b>	110 mm
<b>Clamping diameter</b>	38 mm
<b>Profile shape</b>	Round with transverse grooves
<b>Diameter 2</b>	66 mm
<b>Gross Weight</b>	1.242 kg
<b>Product Group</b>	2AE

### EAN

4053625356577