

Precision pointer

With rubber bellows

ATORN[®]

Application

For measuring lengths. Ideal for measuring instruments and flatness and straightness measurements

Version

- Impact-resistant
- Precision-guided measuring pin
- Connection for wire lifter
- Pointer fine adjustment
- Adjustable tolerance marks
- Measuring mechanism on ruby bearings
- suitable for internal precision measuring instruments
- With rubber bellows

Delivery

In case



Art. No.	33163 025
Calibration Group	K
Scale value	0.01 mm
Length measuring range	0.5 mm
Shaft diameter	8 mm
Shaft length	18 mm
Error limit	12 µm
With free stroke	Yes
Measurement force	1 N
Reversal error	3 µm
IP protection class	IP 53
Repeat accuracy	3 µm
DIN	879

EAN-Code

4050293353259

