

Sliding door cabinet with solid sheet metal doors, height 1200 mm

with shelves, load capacity 80 kg per shelf

Execution:

- Stable welded sheet steel structure with base, available in three different heights, widths and depths
- Galvanised shelves, height-adjustable in increments of 17 mm, load capacity per shelf 80 kg with evenly distributed weight
- Sliding doors with reinforcement pockets and recessed handle, guide rail with special rollers and anti-crush protection, cushioned end stops
- Doors can be locked simultaneously with a push and turn cylinder lock, incl. 2 keys

Delivery:

Available on request: DOM locking system (fits HK tool cabinets, HK tool shelves, HK workbenches) and other paint finishes.

Art. no.	50046 134
Brand	HK
Manufacturer Part Number	50046134
Door design	Full-sheet panel
Height	1200 mm
Depth	400 mm
Width	1000 mm
With partition wall	No
Number of folder height	3 PCS
Number of shelves	2 PCS
Load-carrying capacity per shelf	80 kg
Load-carrying capacity	400 kg
Lock type	Cylinder lock
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Gentian blue RAL 5010
Surface	Powder-coated
Gross Weight	39.000 kg
Product Group	504

EAN

4039247874118