



# Capsuleline

Capsuleline 50W GY6.35 24V CL 4000h 1CT

Single-ended low-voltage halogen capsule giving crisp white halogen light. Compact shape, crisp white light. Low-voltage halogen capsule. Ideal solution for small decorative luminaires. UV-block glass and low-pressure filling allow usage without cover glass. The compact Capsuleline delivers crisp white light over a long lifetime.

## Product data

### • General Characteristics

Philips Code	13090
Cap-Base	GY6.35
Cap-Base Information	15
Bulb	T4 [T4: .434 inch / 11mm]
Bulb Finish	Clear
Operating Position	any [Any or Universal (U)]
Nominal Lifetime	4000 hr
Rated Lifetime (hours)	4000 hr
Rated Lifetime (years)	4 an

### • Light Technical Characteristics

Color Rendering Index	100 Ra8
Color Temperature	3000 K
Color Temperature Technical	3000 K
Luminous flux lamp	850 Lm
Rated Luminous Flux	850 Lm
Luminous Efficacy Lamp	17 Lm/W
LLMF - end nominal lifetime	80 (min) %

### • Electrical Characteristics

Rated Wattage	50.0 W
Lamp Wattage	50 W
Lamp Wattage Technical	50.0 W
Power Factor	1 -
Voltage	24 V
Lamp Current	2.08 A
Dimmable	Yes

Starting Time	0.0 s
Warm-up Time to 60% Light Outp	instant full light

### • Environmental Characteristics

Energy Efficiency Label (EEL)	C
Energy consumption kWh/1000h	53 kWh

### • Measuring Conditions

Switching cycle	16000X
-----------------	--------

### • Luminaire Design Requirements

Pinch Temperature	350 (max) C
Bulb Temperature	900 (max) C

### • Product Dimensions

Overall Length C	44 (max) mm
Diameter D	12 (max) mm
Light Center Length L	30 mm

### • Product Data

Order code	924038720501
Full product code	924038720501
Full product name	Capsuleline 50W GY6.35 24V CL 4000h 1CT
Order product name	Caps 50W GY6.35 24V CL 4000h 1CT/10X10F
Pieces per pack	1
Packing configuration	10X10F


**PHILIPS**

# Capsuleline

Packs per outerbox 100  
Bar code on pack - EAN1 8711500409638  
Bar code on intermediate packing - EAN2 8711500422637


Bar code on outerbox - EAN3 8711500425690  
Logistic code(s) - 12NC 924038720501  
ILCOS code HSG/C-50-24-GY6.35  
Net weight per piece 2.300 gr

## Dimensional drawing



### Capsuleline 50W GY6.35 24V CL 4000h 1CT

Product	C (Max)	D (Max)	L (Norm)
CAP SU 13090 50W GY6.35 24V CL	44	12	30



GY6.35



© 2014 Koninklijke Philips N.V. (Royal Philips)  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2014, November 5  
data subject to change