





Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Fibre optic cable, double ended, PushPull V4, single mode overmoulded

Length: a = 1 m	33 61 221 0010 001
a = 2 m	33 61 221 0020 001
a = 3 m	33 61 221 0030 001
a = 4 m	33 61 221 0040 001
a = 5 m	33 61 221 0050 001
a = 6 m	33 61 221 0060 001
a = 7 m	33 61 221 0070 001
a = 8 m	33 61 221 0080 001
a = 9 m	33 61 221 0090 001
a = 10 m	33 61 221 0100 001
a = 11 m	33 61 221 0110 001
a = 12 m	33 61 221 0120 001
a = 13 m	33 61 221 0130 001
a = 14 m	33 61 221 0140 001
a = 15 m	33 61 221 0150 001
a = 20 m	33 61 221 0200 001
a = 25 m	33 61 221 0250 001
a = 30 m	33 61 221 0300 001
a = 35 m	33 61 221 0350 001
a = 40 m	33 61 221 0400 001
a = 45 m	33 61 221 0450 001
a = 50 m	33 61 221 0500 001
a = 60 m	33 61 221 0600 001
a = 70 m	33 61 221 0700 001
a = 80 m	33 61 221 0800 001
a = 90 m	33 61 221 0900 001
a = 100 m	33 61 221 1000 001



a = length



Fibre optic breakout cable, single mode

Length: 10 m	33 58 751 0100 002
Length: 20 m	33 58 751 0200 002
Length: 100 m	33 58 751 1000 002



PUR jacket
 2-fibre single mode
 Outer diameter: 6.5 mm
 Min. bending radius: 10.4 cm
 Installation: 10.4 cm
 Operating: 5.2 cm