

Cabinets – Varistar CP Electronics

EXTERIOR MOUNTING STEEL DOORS PLAIN

ORDER INFORMATION

					Plain doors			Double Plain door	Handle with round cylinder	Handle for DIN profile half cylinder	Grounding Kit	
					handle with 1 point locking	handle with 1 point locking	handle with 3 points locking	handle with 3 points locking				
 <p>Completely in RAL 7021 (black grey)</p>					 Door St, 1.5 mm, 180° hinge, handle without lever, 2 keys Please order GND/earthing kit separately	 Door St, 1.5 mm, 180° hinge, lever handle with key insert, 2 keys. Please order GND/earthing kit separately	 Door St, 1.5 mm, 180° hinge, lever handle with key insert, 2 keys. Please order GND/earthing kit separately	 Double door St, 1.5 mm, 180° hinge, lever handle with key insert, 2 keys Please order GND/earthing kit separately	 Handle with round cylinder	 Lever handle for 3 points locking	Please order one grounding kit per cabinet frame. The kit is sufficient to ground all components of the cabinet.	
No.	Cabinet dimensions				PU 1 piece assembled	PU 1 piece assembled	PU 1 piece assembled	PU 1 piece assembled	PU 1 piece assembled	PU 1 piece assembled		
	Height	Width	Depth									
	U	mm	mm	mm								
Completely in RAL 7021					RAL 7021	RAL 7021	RAL 7021	RAL 7021				
1	24	1200	600	600	21630-493	21630-400	21630-432	21630-440	24630-098	24630-003		
2	24	1200	600	800	21630-493	21630-400	21630-432	21630-440				
3	29	1400	600	600	21630-495	21630-402	21630-434	21630-442				
4	29	1400	600	800	21630-495	21630-402	21630-434	21630-442				
5	33	1600	600	600	21630-497	21630-404	21630-436	21630-444				
6	33	1600	600	800	21630-497	21630-404	21630-436	21630-444				
7	38	1800	600	600	21630-499	21630-406	21630-438	21630-446				
8	38	1800	600	800	21630-499	21630-406	21630-438	21630-446				
9	38	1800	800	600	21630-500	21630-407	21630-439	21630-447				
10	42	2000	600	300	21630-501	21630-002	21630-104	21630-086				
11	42	2000	600	600	21630-501	21630-002	21630-104	21630-086				
12	42	2000	600	800	21630-501	21630-002	21630-104	21630-086				
13	42	2000	800	600	21630-502	21630-009	21630-107	21630-089				
14	42	2000	800	800	21630-502	21630-009	21630-107	21630-089				
15	47	2200	600	300	21630-503	21630-003	21630-105	21630-087				
16	47	2200	600	600	21630-503	21630-003	21630-105	21630-087				
17	47	2200	600	800	21630-503	21630-003	21630-105	21630-087				
18	47	2200	800	600	21630-504	21630-010	21630-108	21630-090				
19	47	2200	800	800	21630-504	21630-010	21630-108	21630-090				

Other handles

Lever handle ASSA cylinder for 3 point locking (without cylinder)	24630-062
Lever handle KABA cylinder for 3 point locking (without cylinder)	24630-063

DIN profile half cylinder

A) DIN profile half cylinder, key no. 333, qty = 1	60114-121
B) DIN profile half cylinder, push button lockable by keys, Key no. 2233, qty = 1	23130-601

