

1 2 3 4 5 6 7 8

A

A

B

B

C

C

D

D

E

E

F

F

G




G

H

H

**MATERIAL**  
 Insulator : NY66 94V-2  
 Contact Pin : Phorphos bronze

**SPECIFICATION**  
 Current Rate : 3 amperes MAX  
 Insulation Resistance :1000 megohms MAX  
 Contact Resistance : 30mΩMax. at DC 100mA  
 Dielectric Voltage :AC 650 volts RMS at sea level  
 Operation Temperature : -55°C to +105°C



<b>RoHS Compliant</b>		<b>HSM 玄茂科技股份有限公司</b>	
		<b>HSUAN MAO TECHNOLOGY CO., LTD.</b>	
APPD. 核准	DWG. 製圖 <b>Hedy</b>	TOLERANCE 容許公差 .0 =±.30 .00 =±.20 .000 =±.00X .0000=± ANG.=±3°	PART NAME 品名 2.0mm MINI JUMPER 2P H:10.9mm OPEN TYPE GOLD PLATING BLACK COLOR ROHS LOW-LEAD
DATE 制表日 2010/04/22			
PAGE 張數 1 / 1		REV. 版次 A	

1 2 3 4 5 6 7 8