

DESCRIPTION:

Heat-shrinkable tubing in a dispenser box pack

Excellent physical and mechanical properties

Flexible

Flame retardant

RoHS compliant

APPLICATION:

Protects electric wires from corrosion. Can be also used to mark electric wires.

SPECIFICATION:

Dielectric strength 15 kV/mm

Material Polyolefin

Shrink ratio 2:1

Temperature range -55 ... 125 °C

Shrinkage temperature range 70...125 °C

PRODUCT RANGE:

Art. Nr.	Length	Colour	A	B	C
RND 465-00710	15 m	Brown	3 mm	1.5 mm	0.4 mm
RND 465-00711	10 m	Brown	4.5 mm	2.3 mm	0.55 mm
RND 465-00722	10 m	Brown	9 mm	4.5 mm	0.6 mm
RND 465-00723	5 m	Brown	12 mm	6 mm	0.65 mm
RND 465-00724	5 m	Brown	18 mm	9 mm	0.8 mm
RND 465-00725	5 m	Brown	25 mm	12.5 mm	0.9 mm
RND 465-00726	15 m	Grey	3 mm	1.5 mm	0.4 mm
RND 465-00727	10 m	Grey	4.5 mm	2.3 mm	0.55 mm
RND 465-00728	10 m	Grey	9 mm	4.5 mm	0.6 mm
RND 465-00729	5 m	Grey	12 mm	6 mm	0.65 mm
RND 465-00730	5 m	Grey	18 mm	9 mm	0.8 mm
RND 465-00731	5 m	Grey	25 mm	12.5 mm	0.9 mm

