Minitek™ IDC Receptacles 2,00 mm





- Early entry, single-beam contacts provide long wiping action for reliable electrical contact
- Center key polarization and friction latch options
- Single-piece design provides one of the lowest applied costs in the industry

Technical Data

Physical

Housing: Black thermoplastic Flammability rating: UL 94 V-0 Contact: Phosphor-bronze Plating: Gold over 1.27 µm nickel

Electrical Performance

Current rating: 1 A continuous Insulation resistance: 1000 M Ω min. Contact resistance: 30 m Ω max. Dielectric withstanding voltage: 650 V

Mechanical Performance

Mating cycles (durability): 100

Operating Temperature

-40°C to +105°C

Packaging

Tubes

Reference Information

% File no. E66906

File no. LR46923

Product drawing: 89947 or 89361 Product specification: BUS-12-115

Specifications subject to change without notice.


Mating Data


Page ■ Minitek[™] Unshrouded straight headers 38 ■ Minitek[™] Unshrouded right angle headers 40 ■ Minitek[™] Shrouded straight headers 44 ■ Minitek[™] Shrouded right angle headers 46


Insertion Depth

■ 2.55 mm min. to 4.57 mm max. [provides .381 mm wipe]

Typical Applications













Part Number





Dimensions in mm

