



Pocket Multimeter With NCV Function

Basic data:

ID	0000690004
GTIN	7630268415112



Features:

4000 Counts Display with LCD Backlight
 Auto Range Selection
 Diode & Continuity Buzz Check
 0.5~99.0% Duty Cycle Measurement
 Auto Power Off
 Non-Contact ACV Detection
 Flashlight
 Double Mold
 CAT IV 600V

Technical data:

Indication:	Digital
With display backlight:	Yes
Measuring range selection:	Automatic
Max. voltage measuring range, AC:	600 V
Lowest resolution, AC voltage:	1 mV
Max. voltage measuring range, DC:	600 V
Lowest resolution, DC voltage:	0.1 mV
Max. current measuring range, AC:	0.2 A
Lowest resolution, AC current:	0.1 μ A
Max. current measuring range, DC:	0.2 A
Lowest resolution, DC current:	0.1 μ A
Max. resistance measuring range:	40 MOhm
Lowest resolution, resistance:	0.1 Ohm
Capacitance measurement:	Yes
Max. capacitance measuring range:	100 μ F
Lowest resolution, capacitance:	0.00001 μ F
Frequency measurement:	Yes
Max. frequency measuring range:	9.999 kHz
Lowest resolution, frequency:	0.001 Hz
Resistance test/diode test:	Yes
Continuity test:	Yes
Duty cycle measurements:	Yes
Measuring circuit category:	CAT IV
Max. voltage measuring circuit category:	600 V