

**GH506 / GH506B / GH466 /
GH466B / FC325 / GH213
GH810 (-12 to -32)**

Nipples with
wire trap


Nippel mit
Ausreiß-
sicherung

Nipples avec
gorge pour
retenir les
nappes

Nipples con
protezione da
strappo

Manguito
roscados para
seguro de
arranque

GH506(B)/FC325/GH466(B)/GH213/GH810



DSA

DKO Female Swivel, Heavy Duty, 45° Elbow
Dichtkopf DKOS, schwere Baureihe, 45° Krümmer
DKO série S, coude 45°
Femmina girevole DKOS a 45°, serie pesante
Hembra loca DKOS acodado a 45°, serie pesada

Part Number GH506(B)/FC325/ GH810-12,-16	Part Number GH466(B)/GH213-24,-32 GH810-20,-24,-32	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E mm	K Ø mm	HEX [1]	HEX [2]
1W16DSA12.029		M30x2,0		20	19	-12	124,4	72,4	28,2	15,1		36	
1W16DSA12.040		M30x2,0		20	19	-12	135,8	83,8	40,0	15,1		36	
1W20DSA12		M36x2,0		25	19	-12	135,1	83,1	32,0	15,1		46	
1W32DSA12		M52x2		38	19	-12	168,6	116,6	47,0	15,1		60	
1W20DSA16.033		M36x2,0		25	25	-16	145,7	79,1	32,9	19,6		41	
1W25DSA16		M42x2,0		30	25	-16	163,6	97,0	35,0	19,6		50	
1W25DSA16.042		M42x2,0		30	25	-16	164,2	97,5	41,4	19,6		50	
1W25DSA20		M42x2		30	31	-20	195,3	120,4	39,9	25,5		50	
1W32DSA16.063		M52x2		38	25	-16	185,9	119,2	63,0	19,6		60	
1W32DSA20.063	1W32DSA20.063	M52x2,0		38	31	-20	199,4	124,5	63,0	25,5		60	
1W32DSA20	1W32DSA20	M52x2,0		38	31	-20	190,0	115,0	39,0	25,5		60	
1W32DSA24	1W32DSA24	M52x2,0		38	38	-24	198,0	99,0	39,5	30,0		60	