Product Specification PDF



Date	Correct as of 12th May 2020
Brand	с.к
Product	T3778DF
Description	SensoPlus ESD Oblique Cutter Full Flush 120mm
Barcode	5013969687118
Commodity code	8203200000
Country of origin	DE



Features & Benefits

 \sim Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability \sim Precision box joint construction for permanent, adjustment free jaw alignment \sim Induction hardened jaws for outstanding long term performance \sim Mirror polished surface eliminates the risk of damage from flaking chrome \sim Spot welded double leaf springs for consistent, repetitive action \sim Ergonomically designed dual component handles for increased comfort & control \sim Fully ESD compliant for safe use on sensitive electronic components \sim According to IEC 61340 5.1 & 5.2 \sim Wide head, long jaws \sim Bevel: Full Flush Cut \sim Length of cutting edges: 18 mm \sim Overall length: 120 mm \sim Cutting capacities wire: Hard: 0,3 mm / Medium Hard: 1,0 mm / Soft: 1,6 mm

Applicable Standards IEC 61340 5.1 & 5.2 Health & Safety None applicable

Warranty C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through

normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures					
	Product only	Product & primary packaging	Secondary packaging	Transit packaging	
Item Quantity	1	1	0	120	
Width mm	75	57	0	380	
Depth mm	7	25	0	300	
Height mm	125	160	0	360	
Weight	87	106	0	11.7	
Packaging Information	Card use	Box	0	Case	
	Card gms	18	0	350	
	Plastic use	Bag	0	-	
	Plastic gms	1	0	-	
	Metal use	0	0	-	
	Metal gms	0	0	0	
	Timber use	0	0	-	
	Timber gms	0	0	0	