

## POWER DISTRIBUTOR CUBE 67


4x M12, 6-pole

Power distributor 4 × M12  
System accessories

Housing fully potted. For connection cables please see chapter "Connection Technology"


### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



#### General data

Protection	IP67
Mounting method	2-hole screw mounting
Temperature range	0...+55 °C (storage temperature -20...+75 °C)
Dimensions H × W × D	150×30×34.5 mm

#### Voltage output signals

Connection	Female M12, 6-pole
------------	--------------------

Load	max. 4 A
------	----------

**Voltage inputs**

Input voltage	24 V DC (EN 61131-2)
---------------	----------------------

Connection	7/8" male, 5-pole
------------	-------------------

Load	max. 9 A
------	----------

**Module Supply**

Operating voltage	24 V DC (EN 61131-2)
-------------------	----------------------

**Diagnostic**

Monitoring - no voltage	yes
-------------------------	-----

Short circuit and overload	yes
----------------------------	-----

**Commercial data**

country of origin	DE
-------------------	----

customs tariff number	85176200
-----------------------	----------

minimum order quantity	1
------------------------	---