

## Electronic workshop vernier callipers

MAHR MarCal 18 EWR with blade tips



### Application:

For measuring external and internal dimensions.

### Execution:

- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Auto off
- Preset function
- ABS function
- With blade tips

### Advantage:

- Key lock to prevent unintentional adjustment
- Lightweight design with reduced cross-sections, with weight-reducing holes from 500 mm
- Switched on automatically by moving the slider

### Delivery:

In a case, with battery (1 x 3 V lithium type CR 2032)



|   |                    |
|---|--------------------|
| <b>Art. no.</b>                                   | <b>31181 710</b>   |
| <b>Brand</b>                                      | MAHR               |
| <b>Manufacturer Part Number</b>                   | 4112716            |
| <b>Min./max. length measuring range</b>           | 0-1000 mm          |
| <b>Data transmission type</b>                     | multiCOM           |
| <b>IP protection class</b>                        | IP 65              |
| <b>Length of jaw</b>                              | 150 mm             |
| <b>Measuring tips</b>                             | Yes                |
| <b>Fine adjustment</b>                            | No                 |
| <b>Digit increment</b>                            | 0.01 mm            |
| <b>Inner measurement scales</b>                   | 20 mm              |
| <b>Type of locating</b>                           | With locking screw |
| <b>Weight</b>                                     | 2.2 kg             |
| <b>Display</b>                                    | Digital            |
| <b>Calibration Group</b>                          | A                  |
| <b>Number of rechargeable batteries/batteries</b> | 1 PCS              |
| <b>Battery designation</b>                        | 3V CR2032 Lithium  |
| <b>ISO</b>  | 13385-1            |
| <b>Gross Weight</b>                               | 5.600 kg           |
| <b>Product Group</b>                              | 305                |

### EAN

4059192002961