

Shelf boltless rack, single-row

Zinc-plated



Application:


Universal shelving system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools

Execution:

- Shelves height-adjustable in increments of 25 mm for variable adaptation to stored goods
- Shelves with a 50 mm hole grid to accommodate accessories, shelf edge height 40 mm
- For technical reasons, depth reinforcements are always zinc plated, even with coated frames
- Basic rack planning dimensions: Nominal length + 56 mm, nominal depth + 36 mm
- With dismantled or pre-assembled frame

Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



Art. no.	50167 029
Brand	META
Manufacturer Part Number	20088715
Height	2500 mm
Length	1006 mm
Depth	536 mm
Nominal length	1000 mm
Nominal depth	500 mm
Design	Add-on shelving
Type of assembly	To insert
Surface	Zinc plated
Design of the frame	Disassembled
Grid dimension	25 mm
Number of shelves	6 PCS
Load-carrying capacity per shelf	100 kg
Load-carrying capacity per field	1650 kg
Number of frame	1 PCS
Quality label	RAL-RG 614/1
Made in	Germany
Gross Weight	29.477 kg
Product Group	508

EAN

4026212223736