

## SBEV 1000-2 hammer drill

1010 W

**metabo**<sup>®</sup>

### Application:

for drilling boreholes in particularly hard materials using mechanical impact.

### Delivery:

quick-action drill chuck, extra handle, depth stop, in plastic case



<b>Art. no.</b>	<b>70020 191</b>
<b>Brand</b>	METABO
<b>Manufacturer Part Number</b>	600783500
<b>Model</b>	SBEV 1000-2
<b>Manufacturer Article Number</b>	600783500
<b>Nominal voltage</b>	230 V
<b>Max. drilling diameter in steel</b>	16 mm
<b>Max. drilling diameter in wood</b>	40 mm
<b>Max. drilling diameter in concrete</b>	20 mm
<b>Max. drilling diameter in masonry</b>	22 mm
<b>Power input</b>	1010 W
<b>Power output</b>	540 W
<b>Max. impact rate</b>	53200 rpm
<b>Idle speed 1st gear min./max.</b>	0-1000 rpm
<b>Idle speed 2nd gear min./max.</b>	0-2800 rpm
<b>Min./max. drill chuck span width</b>	1.5-13 mm
<b>Drill chuck type</b>	Quick action chuck
<b>Weight</b>	2.7 kg
<b>With rubber-coated handle</b>	Yes
<b>With overload protection</b>	No
<b>With restart protection</b>	Yes
<b>With right/left-hand rotation</b>	Yes
<b>With electronic feedback</b>	Yes
<b>With impulse function</b>	No
<b>Gross Weight</b>	4.440 kg
<b>Product Group</b>	745

### EAN

4007430313119