

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010435](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Crimp Contact Insert, Female, 5-Pole, 16A, for Crimp Contacts, Size 3A «21x21»](#)

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size 3A «21x21»
 Component Type Inserts - Crimp Contact
 Exclude SD Check Yes
 Insert Series S-QD5/0
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
 UPC 887191890432

Physical

Durability (mating cycles max) 500
 Flammability UL 94V-0
 Gender Female
 Insert Color Grey
 Material - Insert Polycarbonate
 Net Weight 13.800/g
 Number of Rows 2
 Packaging Type Bag
 Polarized to Mating Part Yes
 Poles 5
 Temperature Range - Operating -40°C to +125°C

Electrical

Current - Maximum per Contact 16.0A
 Voltage - Maximum 230V / 400V

Material Info

Engineering Number 7605.5801.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93601 Series](#)

Mates With

[93601-0436 Male Crimp Contact Insert](#)

Use With

Turned Contacts - Female