



FEATURES:

- Mates with Model #'s 4771, 4772 or 4741 square pin receptacles.
- The rotating Micrograbber® Test Clip is ideal for testing surface mounted devices (SMDs), high density leads with 1.2 (0.05) spacing, and fine gauge wires 0.1 (0.004).
- Two access entries with 0.6 (.025) square pins.
- Rotating pincers grasp leads firmly.
- Extended guide tube reaches into right areas and can be bent to a 35° angle.

MATERIALS:

Insulation: Nylon

Wire: Steel

RATINGS:

Operating Temperature: +80°C (+176°F) Max

Operating Voltage: 33 VRMS / 70 VDC

Current: 2 Amperes Max

ORDERING INFORMATION: Model 5790-*

*=Color, -0 Black, -2 Red

Ordering Example: 5790-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA