

# MG100S Kit 1

Product no.: U-100-1056-ESDN



## Benefits

- › H13 particle filter and wide band gas filter, for max. 2 workplaces, high gasfilter volume
- › Electronic filter control with filter alarm  
Optical and acustic filter full alarm
- › 3-speed setting  
Variable Speed setting
- › Compact footprint  
Small foot print
- › Switching power supply 100 - 240 V
- › Optimized filter lifetime
- › Applications: Hand soldering, heavy duty and general soldering, gluing, cleaning, filling, and fine dust
- › Can be equipped with optional filter for MEK, VOC, and cleanroom applications
- › Includes MG100S fume extraction unit 120V / 50/60 Hz with H13 particle filter with wide band gas filter



### Technical Data

Dimensions L x W x H (mm)	460 x 210 x 610
Dimensions L x W x H (inches)	18,11 x 8,26 x 24,15
Weight (approx.) in kg	15
Voltage	110 - 240 V, 50/60 Hz
Power	100 W
Noise level (distance 1 m) dB(A)	< 52
Max. vacuum	2300 Pa
Capacity m <sup>3</sup> /h	140
Pre-filter	---
Compact filter	Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb)
Max. capacity	1-2 workstations
RS232 interface (remote control)	---
USB port	---
WX-compatible	---