



TECHNICAL DATA

Item no.	1006825
Number of different light outlets	1
IP Code	IP 20
Impact resistance class	IK 02
Impact resistance	0.2 Joule
Assembly details	Track, Track Ceiling
Dimmable	Yes
Dimming technology	DALI
Primary nominal voltage	48V
Secondary power / voltage	350 mA
Safety class	III
Wattage	16 W
Minimum ambient temperature	-20 °C
Maximum ambient temperature	35 °C
Network rated standby power	0.5 W
Lumen	970 lm
Colour temperature	2700 Kelvin
Beam angle	40 °
Color	white
CRI	90
UGR ≤	16
LXXBXX data	L80B50

Light Source

791819	
--------	---

Accessories

1004786	NUMINOS® S , diffuser Ellipse
1004787	NUMINOS® S , diffuser Prisma
1004788	NUMINOS® S , diffuser Frosted
1004789	NUMINOS® S , diffuser Wabe

Service life	50000 h
Risk Group	1
Height	12.5 cm
Diameter	6 cm
Pendant length	150 cm
Net weight	0.358 kg
Gross weight	0.383 kg