


ADAPTOR M12 MALE 5 POLE/ M12 FEMALE 4 POLE SHIELDED

Adapter
M12 - M12
Male straight to female straight
5-pole, shielded

[Link to Product](#)

Illustration



Product may differ from Image

Form

42265

Technical Data

| | |
|-------------------------------|---|
| Operating voltage | max. 30 V AC/DC |
| Operating current per contact | max. 4 A |
| Locking of ports | Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing |
| Compression gland | Zinc die casting, matte nickel plated |
| Protection | IP67 inserted and tightened (EN 60529) |
| Material | PUR |

General data

| | |
|------------------------|--------------|
| Temperature range | -25...+85 °C |
| Test isolation voltage | 0.8 kVrms |

Commercial data

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Murrelektronik GmbH | Falkenstraße 3, 71570 Oppenweiler | Fon +49 (71 91) 47-0, Fax +49 (71 91) 47-491000 | shop@murrelektronik.de | shop.murrelektronik.de

| | |
|------------------------|----------|
| country of origin | DE |
| customs tariff number | 85369010 |
| minimum order quantity | 1 |
