

Accessory

PICO-LPG-780-1064
Order Number: 70140330

| Main Parameters (*) | min | typ | max | Unit |
|-----------------------|-----|-----|-----|------|
| Operating Temperature | -50 | | 85 | °C |
| Storage Temperature | -50 | | 80 | °C |

Technical Parameters

RoHS yes

Optical Parameters

| | |
|------------------------|--|
| Luminous transmittance | 45.00 % |
| LB Rating | 190-315 D LB8 + IR LB4 315-420 DIR LB5 420-445 DIR LB4 765-1100 DIRM LB5 775-1085 D LB5 + IRM LB6 790-1080 D LB6 + IRM LB7 950-1085 DIRM LB6 |
| Lens Color | Grün |

Mechanical Parameters

| | |
|---------------|---------------|
| Size | 144x145x50 mm |
| Material | Polymer |
| Housing Color | black |
| Weight | 10 g |

(*) Over the complete operating temperature range

Features




- Complete protection
- Comfortable fit over prescription glasses or alone
- Adjustable temples and Side-shields for wide field of view
- CE Certified EN 207
- With Picotronic Logo imprint

Picture



Safety Label



Valid Revision

| 12-FEB-2021