

Micrometer

Baked enamel-finished frame

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:


- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

Advantage:

- Baked enamel-finished frame

Delivery:

Including box, setting standard (from 25 mm), adjustment wrench, up to 50 mm with factory test certificate



| | |
|---|------------------|
| Art. no. | 32016 052 |
| Brand | MITUTOYO |
| Manufacturer Part Number | 103-146-10 |
| Min./max. length measuring range | 225-250 mm |
| Vernier scale | 0.01 mm |
| Measuring surface diameter | 6.3 mm |
| Measuring spindle increments | 0.5 mm |
| Bracket depth | 139 mm |
| Spindle clamping | Yes |
| Error limit | 5 µm |
| Display | Nonius |
| Min./max. measurement force | 5-15 N |
| Calibration Group | D |
| Gross Weight | 2.180 kg |
| Product Group | 3MA |

EAN

4946368215020