

Tipping containers, manual tipping - mobile container with Totalstop brakes

Carrying capacity: up to 800 kg

Application:

For the collection and disposal of all types of bulk goods and solid materials with floor-level emptying option.

Version:

- Skip with sliding handle
- Robust sheet steel construction, double-folded top rim, double-folded dumping edge
- 2 steering and 2 fixed castors, 200 x 40 mm TPE wheels, hubs with grooved ball bearings, Totalstop braking system
- No link chain slide guard (see no. 50266034)

Advantage:

- Totalstop brake system for ideal locking of container for tipping
- With floor-level emptying option



Art. no.	50266 090
Volume	0.6 m ³
Length	1458 mm
Width	855 mm
Tipper edge height	843 mm
Height	1099 mm
Fork pocket clearance	327 mm
Fork pocket size (W x H)	194 x 72 mm
Number of wheels	4
With drain valve	No
With stacker seat tilt function	No
With wheel lock	Totalstop
With perforated sheet	No
Load-carrying capacity	750 kg
Surface	Powder-coated
Colour	Brilliant blue RAL 5007

EAN-Code

4017976047034