

## Balancer with load capacity of 0.4-6.5 kg

Type 7228, cable extraction 1600 mm

AUTOSTAT

### Application:

Can be used with the following tools and devices, e.g. compressed air devices, electric devices, paint spray guns, cable-binding pliers, nailing devices, flue gas swivelling arms, robot power supply line, welding pliers, packaging devices etc.

### Execution:

- Housing made of extremely shock-resistant special plastic
- Suspended with rotating screw snap hooks
- Infinitely adjustable load, via notches
- The load is attached via a safe screw snap hook
- Cable feed limitation is impact absorbing and adjustable
- Rope is infinitely variable in its length via a rope clamp
- If required, the cable can be replaced very easily
- Safety device: Fall arrester in line with DIN 15112 included in scope of delivery, spring safety device, riveted special motive spring, cable drum, can be blocked, push clamp for securing the cable end
- Working area: Cable extraction: 1600 mm, ropes in special lengths available on request

### Advantage:

- Effortless work



<b>Art. no.</b>	<b>77000 587</b>
<b>Brand</b>	AUTOSTAT
<b>Manufacturer Part Number</b>	77000587
<b>Min. load-carrying capacity</b>	1.2 kg
<b>Max. load-carrying capacity</b>	2.6 kg
<b>Type</b>	7228
<b>With automatic locking</b>	No
<b>Max. cable pull-out length</b>	1600 mm
<b>Adjustable cord length</b>	Yes
<b>Wire cable diameter</b>	3 mm
<b>Replaceable cord</b>	Yes
<b>Cord in-feed restriction</b>	Absorbs impacts, adjustable
<b>Material of cable drum</b>	Highly abrasion-proof plastic
<b>Suspension type</b>	Freely rotating and pivot screw karabiner hook
<b>Load attachment</b>	Screw Karabiner hook
<b>Material of housing</b>	Plastic
<b>Housing width</b>	141 mm
<b>Housing thickness</b>	71 mm
<b>Colour of housing</b>	Orange
<b>Height</b>	460 mm
<b>Spring design</b>	Riveted special mainspring
<b>With overrotation protection</b>	No
<b>Spring breakage protection</b>	No
<b>Number of springs</b>	1 PCS
<b>DIN</b>	15112
<b>Gross Weight</b>	1.516 kg
<b>Product Group</b>	772

### EAN

4039247366538