

# CORESHIELD™

## SMOOTH NITRILE COATING

Having the right gloves for the right application is crucial to providing your workers with optimum protection.

Thanks to its high-performance fiber, the Honeywell CoreShield™ range of 22 styles offers complete cut protection from level A/A1 to F/A9, in a choice of 4 various gauges (from 10gg to 18gg) and 3 different coatings.

With CoreShield™, simplified hand protection is at your fingertips.



**CoreShield™**   
**Cut protection made simple**

### INDUSTRIES

Manufacturing, Automotive, Metal stamping, Glass handling, Construction, Logistics

### APPLICATIONS

Please refer to CoreShield™ Selector Guide to choose your Honeywell CoreShield™ gloves

## FEATURES AND BENEFITS



### EASY TO CHOOSE

The color-coded marking system makes it easy for you to choose the gloves you need for your application, according to the new EN 388:2016 European standard and ANSI-105-2016 American standard. Choose by level of cut protection, grip, dexterity and fit.



### EASY TO WEAR

One of the lightest-weight cut-protective gloves on the market, they help to prevent hand fatigue for workers who need to wear them all day long.

Skin-friendly yarns that reduce the allergy risk to wearers. CoreShield™ gloves are certified STANDARD 100 by OEKO-TEX®.

Hand and wrist protection.

Touchscreen resistive and capacitive.



### COST-EFFECTIVE TO BUY


Thumb reinforcement.

CoreShield™ High Performance Coating has special abrasion technology for x2 durability coating.

The washability of the glove material means that even after 5 washing cycles, there are no significant changes in performance or size.

CoreShield™ gloves have a longer life, which in turn translates into less frequent replacements and reduced cost of ownership. Purchasing of CoreShield™ gloves is an investment.

**Honeywell**



**CoreShield™ High Performance Smooth Nitrile coating** is liquid repellent, provides dry grip performance, water and oil proof coating, abrasion resistance, high-level of durability and excellent dexterity.

**CoreShield™ Engineered Yarn** Skin friendly and comfortable material to shield the cut resistant material. Softer skin-friendly yarn in contact with the skin.

## CORESHIELD™ CHOOSE YOUR SMOOTH NITRILE COATING

SKU	PRODUCT NAME & DESCRIPTION	CUT LEVEL & COLOR CODING	EN388:2016 PERFORMANCES	ANSI/ISEA 105:2016 PERFORMANCES		EN407 PERFORMANCES
				CUT	ABRASION	
21-1818B	CoreShield, 18 gauge nylon black liner, nitrile super thin black coating, A1/A	A1 A	4X21A	A1	5	
22-7913B	CoreShield, 13 gauge HPPE black liner, smooth nitrile black coating, A2/B	A2 B	4X42B	A2	6	
23-0913B	CoreShield, 13 gauge HPPE/basalt black liner, smooth nitrile black coating, A3/C	A3 C	4X43C	A3	6	X1XXXX
24-0913B	CoreShield, 13 gauge, HPPE/basalt black liner, smooth nitrile black coating, A4/D	A4 D	4X44D	A4	6	
25-0913B	CoreShield, 13 gauge HPPE/stainless steel black liner, smooth nitrile black coating, A5/E	A5 E	4X42E	A5	6	
26-0913B	CoreShield, 13 gauge HPPE/alloy/basalt black liner, smooth nitrile black coating, A6/F	A6 F	4X44F	A6	6	
28-0910B	CoreShield, 10 gauge HPPE/Kevlar/alloy black liner, smooth nitrile black coating, A8/F	A8 F	4X44F	A8	6	
29-0910B	CoreShield, 10 gauge HPPE/Kevlar/alloy black liner, smooth nitrile black coating, A9/F	A9 F	4X44F	A9	6	

### Washing instructions

- Maximum washing temperature 30°C/86°F mild process
- Do not bleach
- Tumble dry possible at low temperature, exhaust temperature max. 60°C/140°F
- Do not iron
- Do not dry clean

Packaging: Gloves are packed in a plastic bag by inner pack of 10 pairs, 10 inner packs per case (100 pairs).  
 Sizes: from 6/XS to 11/XXL

### Honeywell Safety Products UK Limited

Edison Rd – Basingstoke RG21 6QD  
 United Kingdom Phone: +44 (0) 1256 693 200  
 info-uk.hsp@honeywell.com

### Honeywell Safety Products Europe SAS

Immeuble Edison Paris Nord 2  
 33, rue des Vanesses – CS 55288 Villepinte  
 95958 Roissy CDG Cedex – France  
 +33 (0) 1 49 90 79 79  
 info-export.hsp@honeywell.com

### Industrial Safety PPE Technical Support

Free Phone: 00 800 3344 2803 (free calls in Europe)  
 Phone: +44 (0) 1698 647 087 (paid calls)  
 IS.PPE.TECHSUPPORT.EUROPE@honeywell.com

[www.honeywellsafety.com](http://www.honeywellsafety.com)

HIS\_GLOVES\_CoreShield\_Smooth-  
 Nitrile\_DTS\_ENa\_US\_07/19  
 © 2019 Honeywell International Inc.

THE  
 FUTURE  
 IS  
 WHAT  
 WE  
 MAKE IT

**Honeywell**