



Sample photo

Order symbol: CAB PCQ 302017 T
Product nbr: 8113038
Description: Cabinet, PC
Remarks: Smoked transparent cover

EAN: 6418074011077
EI. number:
 Finland: 3421920
 Electric No. Italy: 7682020
 Electric No. Sweden: 2539176

Including: Base with screws for mounting plate/DIN-rail, internal corner plugs, cover with PUR gasket and CS 12137 cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		300	200	170	EKIV 17	DIN-35 Mounting rail	
inch:		11.8	7.9	6.7	EKIV 27	DIN-35 Mounting rail	
Materials:						FP A 23	Swing-out door/Front plate
Material:		Polycarbonate			MB 12225 AL	Swing door set	
Base colour:		RAL 7035 -light grey			FP 12-23	Front plate	
Cover screws material:		Polyamide			DRF 23	DIN rail frame set	
Cover colour:		Smoked grey			DRF 33	DIN rail frame set	
Cover screws colour:		RAL 5023			PAT 12040	Hinge set	
Gasket material:		Polyurethane					
Temperatures:						Rating:	
Temperature °C (short term):		-40 ... 120 °C			Ingress Protection (EN 60529): IP66/IP67		
Temperature °C (continuous):		-40 ... 80 °C			Impact Resistance (EN 62262): IK08		
Temperature °F (short term):		-40 ... 250 °F			Electrical insulation: Totally insulated		
Temperature °F (continuous):		-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1		
Accessories:						UV resistance: UL 508	
EKIV 23		Mounting plate			Flammability Rating: UL 746C 5"		
						Glow Wire Test (IEC 695-2-1) °C: 960	
						NEMA Class: NEMA 1, 4, 4X, 12, 13	
						Certificates:	
						SGS Fimko	

