


E11255



Wirable plug

SSTGF040MSSFKPG



Application	
Special feature	Gold-plated contacts
Electrical data	
Operating voltage [V]	< 30 DC
Outputs	
Electrical design	PNP
Operating conditions	
Ambient temperature [°C]	-25...85
Protection	IP 67
Mechanical data	
Weight [g]	11.5
Dimensions [mm]	12 x 12 x 50
Materials	PA
Material nut	brass, nickel-plated
Remarks	
Pack quantity	1 pcs.
Electrical connection	
screw terminals: 0.14...0.5 mm ² ; Cable sheath: Ø 3.5...5 mm	
Electrical connection - plug	
Connector: 1 x M8, straight; Moulded body: PA; Locking: brass, nickel-plated; Contacts: gold-plated	

E11255

Wirable plug

SSTGF040MSSFKPG



Connection

