



M8 FEMALE FLANGE PLUG A CODED FRONT MOUNT

Wires 3x0.25 0.8m

Front mounting
Flange M8 female
with multi-strand wire
3-pole

[Link to Product](#)**Illustration**

Female



Product may differ from Image

Form

08571

Technical Data

| | |
|-------------------------------|--|
| Operating voltage | max. 60 V AC/DC |
| Operating current per contact | max. 4 A |
| Locking of ports | Screw thread M8 × 1 mm (recommended torque 0.4 Nm) self-securing |
| Protection | IP67 inserted and tightened (EN 60529) |

Cables

| | |
|-----------------------------|--------------------------|
| Cable number | 970 |
| No./diameter of wires | 3 × 0.25 mm ² |
| Wire isolation | PP (br, bk, bl) |
| Shore hardness outer jacket | 70 ± 5D |
| Outer diameter | approx. 1.25 mm |
| Bend radius (fixed) | 5 × outer Ø |
| Bend radius (moving) | 10 × outer Ø |
| Temperature range (fixed) | -40...+80 °C |
| Temperature range (mobile) | -25...+80 °C |

Commercial data

| | |
|------------------------|----------|
| country of origin | DE |
| customs tariff number | 85444290 |
| minimum order quantity | 1 |