

Ultrasonic transit time Sensor Clamp-On, Universal Size, A2, pair, dediziert, Ex Zone 0,1,2, Class 1, Div 1,2, any pipe materials, Liquid, Pipe Diameter range 12.7 - 50 mm (0.5 - 2"), Temperature -40C - +121C (-40F - +250F) Housing Polyetherimide/StSt corrosion resistant, for FST020, FST030, (substitute for FUx1010)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.de/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com>