



Strom
Current
Spannung
Voltage
Frequenz
Frequency

Stecker Plug

IP 44

Kupplungsdose Coupler

IP 44

Isogekapselt Schraubanschluss · In plastic enclosure screwed connection

A	V	Hz	Typ Type	Best.-Nr. Ref. No.	VPE PU	Typ Type	Best.-Nr. Ref. No.	VPE PU
16	400	50/60	CT 516/6h	50 516	10	CC 516/6h	51 516	10
32	400	50/60	CT 532/6h	62 879	10	CC 532/6h	62 880	10
63	400	50/60	CT 563/6h	82 183	2	CC 563/6h	82 184	2

5-polig poles:
3 P + N + ⊕



Stecker Plug

IP 44

Phasenwender, isogekapselt Schraubanschluss · Phase inverter, in plastic enclosure screwed connection

A	V	Hz	Typ Type	Best.-Nr. Ref. No.	VPE PU
16	400	50/60	CTP 516/6h	82 923	10
32	400	50/60	CTP 532/6h	82 683	10

5-polig poles:
3 P + N + ⊕



**Wandsteckdose
Wall mounting socket**

IP 44



**Anbausteckdose für senkrechte Montage
Socket for vertical mounting**

IP 44

Isogekapselt Schraubanschluss · In plastic enclosure screwed connection

A	V	Hz	Typ Type	Best.-Nr. Ref. No.	VPE PU	Typ Type	Best.-Nr. Ref. No.	VPE PU
16	400	50/60	CO 516/6h	62 874	10	CLU 516/6h Flansch 85x85 mm	312 289	10
						CLU 516/6h Flansch 80x75 mm	312 920	10
32	400	50/60	CO 532/6h	62 878	10	CLU 532/6h	312 845	10
63	400	50/60	CO 563/6h	82 182	2	CLU 563/6h	94 554	2

5-polig poles:
3 P + N + ⊕



IP 44

**Anbausteckdose für gerade Montage
Socket for mounting in straight direction**

Isogekapselt Schraubanschluss · In plastic enclosure screwed connection

A	V	Hz	Typ Type	Best.-Nr. Ref. No.	VPE PU
16	400	50/60	CLS 516/6h Flansch 75x75 mm	189 788	10
32	400	50/60	CLS 532/6h	189 954	10

5-polig poles:
3 P + N + ⊕