

Fast trunking System - Electronic

FTS-LED 1720MM 4000K NR

0052198



Product features

- Fast Trunking System LED linear luminaire for industrial and commercial applications. 1.72 m length with narrow optics provide homogenous light distribution for aisles and focus areas. -20 to + 35 operating temperature range, 4000K, CRI 80, UGR <23, 3 SDMC. 59 W power consumption, 9000 lm luminous flux, 152 lm/W efficacy, luminaire energy class A++. 1720mm x 60 mm x 88 mm (L x W x H) dimensions, IP20, IK03. 220-240V 56/60 Hz, Class I.



PRODUCT OVERVIEW

Product name	FTS-LED 1720MM 4000K NR
Technology	LED
Mount	Ceiling surface mounting, Suspended
Fixture rating	Enclosed
General application	Logistics & Industry
ETIM Class	EC000986
Warranty	5 years
Fixture luminous flux (lm)	9000
Luminaire efficacy (lm/W)	152
LOR (%)	100
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 23
Photobiological Risk Group	RG0
Total power consumption (W)	59
Electrical protection	Class I
Housing colour	White
IP rating	IP20
IK rating	IK03
Product EAN number	5410288521985

DATA TABLE

General data

Product name	FTS-LED 1720MM 4000K NR
Technology	LED
Mount	Ceiling surface mounting, Suspended
Fixture rating	Enclosed
General application	Logistics & Industry
Operating temperature range (°C)	-20°C...+35°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC000986
Warranty	5 years

Fast trunking System - Electronic

FTS-LED 1720MM 4000K NR
0052198

Optical data

Fixture luminous flux (lm)	9000
Luminaire efficacy (lm/W)	152
LOR (%)	100
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 23
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	59
Mains voltage (V)	220-240V
Electrical protection	Class I
Drive current (mA)	700
Nominal Frequency (Hz)	50/60Hz

Lifetime data

Lifespan L70 B50	80000
Lifespan L80 B50	50000

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK03
Nominal Product Length (mm)	1720
Nominal Product Width (mm)	60
Nominal Product Height (mm)	88
Weight (kg)	3.31

Packaging

Single packaging type	Carton
Product EAN number	5410288521985
Packaging single length / height (cm)	198.0
Packaging single width (cm)	9.0
Packaging single depth (cm)	6.7
DUN14 (outer)	05410288521985
Units per outer package	1
Packaging outer length / height (cm)	198.0
Packaging outer width (cm)	9.0
Packaging outer depth (cm)	6.72

Safety data



Optimal operating condition (°C)	-20-35
----------------------------------	--------

Fast trunking System - Electronic

FTS-LED 1720MM 4000K NR

0052198

PHOTOMETRY



TECHNICAL DRAWINGS

