

SRGC clamping holder, positive, right

For copy, longitudinal face lathing with RC indexable insert

ATORN[®]

Application

For longitudinal turning with RC indexable insert

Version

- Precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17850 504
ISO name	SRGC R/L 2020 K06
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	15.3 mm
Programming size	25 mm
Suitable for indexable inserts	RC.. 0602..
Tool design	Right

EAN-Code

4050293563016