

“Nightwatchman“ LED machine lamp

IP 67, 250 mm



Execution:

- high-performance LED in aluminium housing, rotatable
- Light temperature: cold white, approx. 5500 Kelvin, high-performance chip
- 120 degree uniform illumination, anti-glare and flicker-free, low-reflection
- connection to 24 V machine controller or to 230 V power pack
- 2 x 43 mm rubber-coated magnets each with 85 N retention force.
- 9.0 W/1200 lumen, 250x40 mm

Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use

Delivery:

including power pack



Art. no.	56886 070
Brand	BAUER & BÖCKER
Manufacturer Part Number	900/53
Power rating	9 W
Length	250 mm
IP protection class	IP 67
Gross Weight	1.000 kg
Product Group	5ID

EAN

4260131235498