

# RSP-5018 (Artikel-Nr. 183035)

# EKULIT

## SPECIFICATIONS:

TYPE	UNIT	RSP-5018
• Min. Sound Output at 100cm	dB	>105/12V
Rated Voltage	V	12
Operating Voltage	V	6~14
Operating Frequency	Hz	1.500~3.500
• Max. Current Consumption	mA	150/12V
Sweep(pulse) rate/at12VDC		3.3±20%
Operating Temperature	°C	-20~+60
Storage Temperature	°C	-30~+70
Terminal		wire

• Value applying at rated voltage (DC)

## DIMENSIONS :

(Unit: mm)

