

# ANSI PVC Insulated Thermocouple Cable with Plug and Socket

ANSI Colour Coded

---



Type K with Mini Connectors



Type K with Standard Connectors

## Cable Description

- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension type K, 2 or 5 Metre lengths available
- Conductors 7/0.2mm
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) in accordance with ANSI specification

## Connector Description

- Ideal for general purpose use
- All contacts are polarised to ensure correct connection
- Colour coded in accordance with ANSI specification
- Maximum continuous operating temperature 220 deg°C

Ordering Information

Type	Length	Connector Size	Description	Order Number
K	2 metre	Miniature	EXT-K-C1-2.0-MP-MS(ANSI)	XE-7024-001
K	5 metre	Miniature	EXT-K-C1-5.0-MP-MS(ANSI)	XE-7025-001
K	2 metre	Standard	EXT-K-C1-2.0-SP-SS(ANSI)	XE-7026-001
K	5 metre	Standard	EXT-K-C1-5.0-SP-SS(ANSI)	XE-7027-001

