




ESTGH040MSS00.5E04 (PG9)

Connection technology



1: O-ring

Product characteristics

Adapter plug

M12 connector

PG 9 - M12

Electrical data

Electrical design

AC/DC

Operating voltage [V]

250 AC/DC

Current rating [A]

4; (...40 °C)

Environment

Ambient temperature [°C]

-25...85

Protection

IP 67

Mechanical data

Design

straight

Housing materials

diecast zinc nickel-plated

Weight [kg]

0.018

Electrical connection


Connection

PVC cable / 0.5 m; 4 x 0.25 mm<sup>2</sup>

Wiring

Core colours

BK black  
BN brown  
BU blue  
WH white



Remarks

Pack quantity

[piece]

1