

MODLINK MSDD DATA INSERT

2×USB-A female/female + 1xRJ45 + 1xRJ12

1 × RJ45, 8-pole metal, CAT5e (female/female)

1 × RJ12, 6-pole plastic

2 × USB (female/female) form A

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



General data

Dimensions H × W × D 87.5×50.7×70.4 mm

Insert 2

Article number 4000-68000-0910000

Operating voltage SUB-D: max. 125 V AC/150 V DC; RJ45: max. 48 V AC/DC; RJ12: max. 48 V AC/DC; USB: max. 30 V AC/DC; PS2: max. 30 V AC/DC; DVI: max. 40 V AC

Operating current SUB-D: max. 3 A; RJ45: max. 1 A; RJ12: max. 1 A; USB: max. 1 A; PS2: max. 1 A; DVI: max. 1.5 A

Connection cross section SUB-D: max. 0.5 mm² (AWG 20); PS2: max. 0.22 mm² (AWG 24)

Locking of ports SUB-D: UNC 4...40 bolt; RJ45: staple; RJ12: staple; USB: snap-in; PS2: snap-in

Specification	SUB-D: (DIN 41652/IEC 60807-1); RJ45: CAT5e (100 MHz - Mbit/s); USB: 2.0/Type 2dB (max. 480 Mbit/s)
Mounting depth mounted	SUB-D: approx. 32 mm; RJ45: approx. 32 mm; RJ12: approx. 32 mm; USB: approx. 80 mm; PS2: approx. 32 mm
Dimensions H x W x D	88x51x70.4
Shielded	yes
Commercial data	
country of origin	CZ
customs tariff number	85369010
minimum order quantity	1