

Stacking high flow valves with air pilot or solenoid actuation. Lightweight plastic bodies feature push-in or threaded connections. Stacking valves feature modular inlet and exhaust facility.



- High flow, compact size
- Push-in or threaded connection
- DIN rail or block mounting
- Light weight construction



For ATEX specific products contact Sales Office

Operating information







Working pressure;
 Pneumatically operated: 2-10 bar
 Electrically operated, bistable: 2-10 bar
 Electrically operated, monostable: 3-10 bar
 Working temperature -15 °C to +60 °C

	PVL-B	PVL-C
Flow (Qmax):	900 l/min	1800 l/min
Flow Qn:	540 l/min	1100 l/min

Flow measured with valve stacked in island.

PVL-B & PVL-C Valve body - Stand alone and stackable design - Without pilot

Pneumatic or 15 mm electric pilot must be ordered separately

Symbol	Description	Valve size	Connection	Weight (g)	Stand Alone	Stackable
					Order code	Order code
	5/2 single acting / Spring return	PVL-B	Push-in Ø 6 mm	125	PVL-B111606	PVL-B121606
			G 1/8	125	PVL-B111618	PVL-B121618
		PVL-C	Push-in Ø 8 mm	240	PVL-C111608	PVL-C121608
			G 1/4	240	PVL-C111619	PVL-C121619
	5/2 single acting / Air spring return	PVL-B	Push-in Ø 6 mm	125	PVL-B113606	PVL-B123606
			G 1/8	125	PVL-B113618	PVL-B123618
		PVL-C	Push-in Ø 8 mm	240	PVL-C113608	PVL-C123608
			G 1/4	240	PVL-C113619	PVL-C123619
	5/2 double acting	PVL-B	Push-in Ø 6 mm	120	PVL-B112606	PVL-B122606
			G 1/8	120	PVL-B112618	PVL-B122618
		PVL-C	Push-in Ø 8 mm	230	PVL-C112608	PVL-C122608
			G 1/4	230	PVL-C112619	PVL-C122619
	5/3 APB (All Ports Blocked)	PVL-B	Push-in Ø 6 mm	130	PVL-B117606	PVL-B127606
			G 1/8	130	PVL-B117618	PVL-B127618
		PVL-C	Push-in Ø 8 mm	250	PVL-C117608	PVL-C127608
			G 1/4	250	PVL-C117619	PVL-C127619
	5/3 Vented centre	PVL-B	Push-in Ø 6 mm	130	PVL-B118606	PVL-B128606
			G 1/8	130	PVL-B118618	PVL-B128618
		PVL-C	Push-in Ø 8 mm	250	PVL-C118608	PVL-C128608
			G 1/4	250	PVL-C118619	PVL-C128619
	Double 3/2 Normally Closed (NC)	PVL-B	Push-in Ø 6 mm	130	PVL-B115606	PVL-B125606
			G 1/8	130	PVL-B115618	PVL-B125618