


**ART.: 8607891273300**

FL SQUARE 600 IL OP



Art.: 8607891273300, FL SQUARE IL, Direct, 22W, 3000K, Driver static, 596mm, Symmetrical, > 75°, White, Lay-in LED luminaire for indoors, consisting of: Die-cast aluminium housing, powder-coated / LED Sidelight-Technology and light orienting plastic optic for a homogenous light distribution over the entire area of the cover / Colour rendering index Ra > 80 / Colour tolerance according to MacAdam = 3 SDCM / Suitable for lattice and coffered ceilings / Complete with electric converter / UGR <19 for all luminosities / VDU application suitable acc. to EN 12464-1 / Protection class IP43 (for light emission surface for installation in closed ceilings) / Recessed luminaire can only be used for cut ceilings with separately available installation frames / Separate accessory allows the lights to be used as a suspended, surface mounted or recessed luminaires

<b>Connected load</b>	22 W
<b>Luminous flux</b>	2790 lm
<b>Efficiency</b>	127 lm/W
<b>Colour temperature</b>	3000K
<b>Colour rendering (CRI)</b>	80
<b>IP class</b>	20
<b>Nominal voltage</b>	220 – 240 V
<b>Colour</b>	WH-RAL9016
<b>UGR</b>	≤ 22

