

RouteLED 2 ROUTELED II CORRIDOR 2059460



Product features

- Miniature emergency recessed luminaire downlight with corridor optic, non-maintained 3 hr emergency, standalone unit with inverter module and rechargeable battery (NiMH), quick and easy installation with inverter module and battery pack contained in articulated case that can pass through 40mm cutout, 219lm, 3W, IK07, beam angle 148 degrees, 230V, 50-60Hz, recharge period 24 hours, Power Factor 0.45, charge current 300mA, LxWxD (mm) 416x29x26.



PRODUCT OVERVIEW

Product name	ROUTELED II CORRIDOR
Technology	LED
Type	Integrated LED
Housing	Aluminium
Mount	Ceiling recessed mounting
General application	Office, Hospitality, Retail, Education
ETIM Class	EC001957
Warranty	5 years
Fixture luminous flux (lm)	212
LOR (%)	100
Colour temperature (K)	5000
Light colour	Cool White
CRI (Ra)	70
Colour Variation Initial (SDCM)	SDCM5
Colour Consistency (SDCM)	5
Beam Angle (°)	158
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	219
Luminous flux (emergency) (lm)	219
Product Voltage (V)	230
Electrical protection	Class II
Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK07
Product EAN number	5025768594603

DATA TABLE

General data

Product name	ROUTELED II CORRIDOR
Technology	LED
Type	Integrated LED
Housing	Aluminium
Mount	Ceiling recessed mounting

RouteLED 2

ROUTELED II CORRIDOR

2059460

General application	Office, Hospitality, Retail, Education
Operating temperature range (°C)	0°C...+35°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001957
Warranty	5 years

Optical data

Fixture luminous flux (lm)	212
LOR (%)	100
Colour temperature (K)	5000
Light colour	Cool White
CRI (Ra)	70
Colour Variation Initial (SDCM)	SDCM5
Colour Consistency (SDCM)	5
Beam Angle (°)	158
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	219
Luminous flux (emergency) (lm)	219
Emergency duration (h)	3

Electrical data

Mains voltage (V)	230-240V
Product Voltage (V)	230
Electrical protection	Class II
Drive current (mA)	200
Glow Wire Test (°C)	850
Nominal Frequency (Hz)	50/60Hz

Physical data

Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK07
Nominal Product Length (mm)	416
Nominal Product Width (mm)	27
Nominal Product Height (mm)	27
Cutout Dimensions (W x L in mm or Diameter in mm)	40
Weight (kg)	0.948
Recessed Depth (mm)	80

Packaging

Single packaging type	Carton
Product EAN number	5025768594603
Packaging single length / height (cm)	21.0
Packaging single width (cm)	18.0
Packaging single depth (cm)	11.0
Units per outer package	1
Packaging outer length / height (cm)	21.0
Packaging outer width (cm)	18.0

RouteLED 2 ROUTELED II CORRIDOR 2059460

Packaging outer depth (cm) 10.5

Safety data

Optimal operating condition (°C) 0-35

Dry applications use only Yes


PHOTOMETRY

Distance [m]	Cone diameter [m]	E(0°)	E(C90)	E(C0)	Illuminance [lx]
0.5	5.40 1.04	246	79.5°	45.0°	41
1.0	10.79 2.07	91	79.5°	45.0°	10
1.5	16.19 3.11	27	79.5°	45.0°	6
2.0	21.58 4.14	16	79.5°	45.0°	3
2.5	26.98 5.18	10	79.5°	45.0°	2
3.0	32.37 6.21	7	79.5°	45.0°	1

Distance [m] Cone diameter [m] Illuminance [lx]

— C0 - C180 (Half beam angle: 92.0°)

— C90 - C270 (Half beam angle: 159.0°)



TECHNICAL DRAWINGS

