

Inset Trend 75 Swing IP44 Outdoor


INSET TREND SW IP44 OUTD AN EX LMP

3099390



Product features

- 75mm cut out. 2 x 25° Tilt. Round bezel.



PRODUCT OVERVIEW

Product name	INSET TREND SW IP44 OUTD AN EX LMP
Technology	LED/Halogen
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271331
E-number SE	7463930
Warranty	3 years
LOR (%)	Dependent on lamp
Light source included	Fixture without Lightsource
Electrical protection	Class II
Housing colour	Anthracite
IP rating	IP44/20
IK rating	IK02
Product EAN number	8711971993902

DATA TABLE

General data

Product name	INSET TREND SW IP44 OUTD AN EX LMP
Technology	LED/Halogen
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271331
E-number SE	7463930
Warranty	3 years

Inset Trend 75 Swing IP44 Outdoor INSET TREND SW IP44 OUTD AN EX LMP 3099390

Optical data

LOR (%)	Dependent on lamp
Adjustable chromaticity	N

Electrical data

Light source included	Fixture without Lightsource
Mains voltage (V)	220-240V
Electrical protection	Class II
Transformer required	No
Nominal Frequency (Hz)	50/60Hz

Physical data

Housing colour	Anthracite
IP rating	IP44/20
IK rating	IK02
Nominal Product Length (mm)	95
Nominal Product Width (mm)	95
Nominal Product Height (mm)	100
Cutout Dimensions (W x L in mm or Diameter in mm)	75
Weight (kg)	0.177
Recessed Depth (mm)	100

Packaging

Single packaging type	Carton
Product EAN number	8711971993902
Packaging single length / height (cm)	13.11
Packaging single width (cm)	10.09
Packaging single depth (cm)	8.48
DUN14 (outer)	18711971993909
Units per outer package	30
Packaging outer length / height (cm)	28.8
Packaging outer width (cm)	28.7
Packaging outer depth (cm)	53.0

TECHNICAL DRAWINGS

