

TOLEDO CANDLE DIMMABLE

ToLEDo CAND V4 DIM FROSTED 470LM E14 SL

0026935



Product features

- Compact and elegant design
- Suitable replacement for halogen, incandescent and compact fluorescent candle lamps
- Instant light at the flick of a switch
- Uniform light distribution
- Good colour rendering (CRI 80)
- Dimmable with approved dimmers
- Perfect for hotels, restaurants, lobbies, corridors, stairwells, reception areas
- Lower maintenance costs
- A+ energy rating



PRODUCT OVERVIEW

Product name	ToLEDo CAND V4 DIM FROSTED 470LM E14 SL
Technology	LED
Watt (Rated) (W)	5.6
Type	TOLEDO CANDLE DIMMABLE
Cap/Base	E14
Fixture rating	Open
General application	Hospitality, Education, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740197
E-number SE	8296540
Warranty	3 years
Luminous flux (lm)	470
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Beam Angle (°)	280
Wattage (W)	5.6
Product Voltage (V)	230
Dimmable	Yes
Average life (Nominal) (h)	15000
Product EAN number	5410288269351

DATA TABLE

General data

Product name	ToLEDo CAND V4 DIM FROSTED 470LM E14 SL
Technology	LED
Watt (Rated) (W)	5.6
Type	TOLEDO CANDLE DIMMABLE
Cap/Base	E14
Fixture rating	Open
General application	Hospitality, Education, Residential & Consumer

TOLEDO CANDLE DIMMABLE

ToLEDo CAND V4 DIM FROSTED 470LM E14 SL

0026935

Performance ambient temperature Tq (°C) 25

ETIM Class EC001959

E-number FI 4740197

E-number SE 8296540

Warranty 3 years

Optical data

Luminous flux (lm) 470

Luminous flux (Rated) (lm) 470

Colour temperature (K) 2700

Light colour Homelight

CRI (Ra) 80

Beam Angle (°) 280

Electrical data

Wattage (W) 5.6

Starting time (max) (s) <0.5

Warm-up time to 60% of full light (max) (s) <1.0

Mains voltage (V) 220-240V

Product Voltage (V) 230

Lamp power factor 0.5

No. Of switching cycles before premature failures >50000

Dimmable Yes

kWh per 1000 hours burning time 6

Nominal Frequency (Hz) 50/60Hz

Lifetime data

Average life (Nominal) (h) 15000

Average life (Rated) (h) 15000

Physical data

Nominal Product Length (mm) 110

Nominal Product Diameter (mm) 38

Weight (kg) 0.041

Packaging

Single packaging type Carton

Product EAN number 5410288269351

Packaging single length / height (cm) 12.5

Packaging single width (cm) 4.8

Packaging single depth (cm) 4.8

Units per inner package 6

Packaging inner length / height (cm) 15.0

Packaging inner width (cm) 10.5

Packaging inner depth (cm) 15.3

DUN14 (outer) 15410288269358

Units per outer package 60

TOLEDO CANDLE DIMMABLE

ToLEDo CAND V4 DIM FROSTED 470LM E14 SL

0026935

Packaging outer length / height (cm)	55.2
Packaging outer width (cm)	17.6
Packaging outer depth (cm)	33.6

Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures