

## Electronic 3-point internal micrometer

Micromar 44 EWR, carbide-tipped measuring surfaces, lightweight measuring head made from aluminium



### Application:

For measuring through holes and blind bores and short centring shoulders in series.

### Execution:

- Self-centring and self-aligning
- Carbide-tipped measuring faces
- Locking function
- Zero setting at any position
- mm/inch changeover
- ABS function
- Preset function

### Advantage:

- Lightweight measuring head made of aluminium

### Delivery:

Single device with battery (1 x 3 V lithium, type CR 2032) and operating instructions in a case



<b>Art. no.</b>	<b>31912 040</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4191129
<b>Min./max. length measuring range</b>	40-50 mm
<b>Measuring depth</b>	76 mm
<b>Data transmission type</b>	multiCOM
<b>Digit increment</b>	0.001 mm
<b>IP protection class</b>	IP 52
<b>Error limit</b>	0.004 mm
<b>Display</b>	Digital
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	3V CR2032 Lithium
<b>DIN</b>	863
<b>Calibration Group</b>	I
<b>Gross Weight</b>	1.279 kg
<b>Product Group</b>	305

### EAN

4059192010973